



UltraVision SPECIALTY 55AB

Controls both inherent spherical aberration and that induced on-eye by lens drape

Provides improved acuity, especially under low-light conditions, and for masking low-moderate astigmatism and early presbyopia

Benefits

- Advanced aberration control to increase optical clarity. Apspheric design for enhanced vision.
- Easy to handle first time and experienced wearers.
- Thin consistent edge for maximum comfort.



Material	Methalfilcon A	Powerrange	-12.00 to + 6.00 -6.00 to +4.00 (in 0.25 steps) -12.00 to +6.50 (in 0.50 steps) +4.50 to +6.00 (in0.50 steps)
Water content	55%	DK	23,43x10 ⁻¹¹ (cm ² /sec) [ml O ₂ / (ml x mm Hg)]
Base Curve	8.70 mm	Wear modality	Replacement monthly/two weeks as required for daily wear only
Diameter	14.50 mm	Pack size	3 or 6 lenses
Handling tint	Light blue	Trial lens available as single blister in all parameters	

